

MLFB-Ordering data

6SL3203-0BB21-8VA0



Client order no. : Item no. :
Order no. : Consignment no. :
Offer no. : Project :
Remarks :

Rated data		Co	Connections	
Input		Line side		
Number of phases	1 AC	Version	screw-type terminal	
Line voltage	200 240 V	Conductor cross-section	0,3 10,0 mm ²	
Output		Load side		
Rated current	18.0 A	Version	Screw-type terminals	
		Cable length	20.00 m	
Mechanical data		PE connection		
Dimensions		Version	On housing with M5 screw studs	
Width	59.0 mm			
Height	155.0 mm			
Depth	53.0 mm			
Degree of protection	IP20 / UL open type			
Net weight	0.9 kg			