Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road East Syracuse, NY 13057, USA

Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net
Internet: www.jumousa.com



Data Sheet 705070

Page 1/17

JUMO variTRON Web Panels

705070

Brief description


JUMO variTRON web panels can be easily connected to automation systems of the JUMO variTRON series via Ethernet connection. The web panels support CODESYS Remote TargetVisu or WebVisu. As a result, visualizations created with CODESYS can be displayed on the web panels and used to operate the system. The prerequisite for this is the corresponding extra code of the JUMO variTRON central processing unit: For visualization by means of a browser, extra code 281 (WebVisu) is required; for visualization via Remote TargetVisu, extra code 280 must be selected.

In principle, web panels other than those offered by JUMO can also be used together with an automation system of the JUMO variTRON series, provided that they support the required CODESYS visualization.



Type 705070/...

System structure



Features

- TFT colour screen, resistive or capacitive
- Multi-touch operation (capacitive), also with gloves
- Screen sizes (diagonal) from 10.9 cm (4.3") to 54.6 cm (21.5")
- Screen resolutions from 480 × 272 to 1920 × 1080
- Panel mounting or variable fastening
- Connection to the central processing unit via Ethernet interface
- Voltage supply DC 24 V or PoE
- Versions for food industry
- UL and DNV GL approval (type dependent)

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6733 Myers Road


East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

EXOR Standard eX

eX707 - Type 705070/1-x-10-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation
Screen size (diagonal)	Approx. 17.8 cm (7")
Resolution	800 × 480
Number of colors	16M
Brightness (luminance) typ.	500 cd/m ²
Backlight	LED (dimmable)
Interfaces	3 × Ethernet, 2 × USB host, 1 × serial
Voltage supply	DC 24 V (10 to 32 V)
Current consumption	0.7 A at DC 24 V
Installation type	Installation in panel cut-out
Dimensions L × H × (D + T)	187 mm × 147 mm × (47 + 8) mm
Front panel depth T	8 mm
Mounting depth D	47 mm
Panel cut-out A × B	176 mm × 136 mm
Weight	1.5 kg
Protection type	IP66 (front side), IP20 (rear side)
Operating temperature range	-20 to +60 °C (vertical mounting)
Storage temperature range	-20 to +70 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus, DNV GL
Model (www.exorint.com)	eX707

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road


East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

Page 3/17

eX710 - Type 705070/1-x-20-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation
Screen size (diagonal)	Approx. 25.7 cm (10.1")
Resolution	1280 × 800
Number of colors	16M
Brightness (luminance) typ.	500 cd/m ²
Backlight	LED (dimmable)
Interfaces	3 × Ethernet, 2 × USB host, 1 × serial
Voltage supply	DC 24 V (10 to 32 V)
Current consumption	1.0 A at DC 24 V
Installation type	Installation in panel cut-out
Dimensions L × H × (D + T)	282 mm × 197 mm × (56 + 8) mm
Front panel depth T	8 mm
Mounting depth D	56 mm
Panel cut-out A × B	271 mm × 186 mm
Weight	2.5 kg
Protection type	IP66 (front side), IP20 (rear side)
Operating temperature range	-20 to +60 °C (vertical mounting)
Storage temperature range	-20 to +70 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus, DNV GL
Model (www.exorint.com)	eX710

Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

Internet: www.jumo.co.uk

Email:

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29

sales@jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road East Syracuse, NY 13057, USA


Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

Page 4/17

eX715 - Type 705070/1-x-30-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation
Screen size (diagonal)	Approx. 39.6 cm (15.6")
Resolution	1366 × 768
Number of colors	16M
Brightness (luminance) typ.	400 cd/m ²
Backlight	LED (dimmable)
Interfaces	3 × Ethernet, 2 × USB host, 1 × serial
Voltage supply	DC 24 V (10 to 32 V)
Current consumption	1.2 A at DC 24 V
Installation type	Installation in panel cut-out
Dimensions L × H × (D + T)	422 mm × 267 mm × (56 + 8) mm
Front panel depth T	8 mm
Mounting depth D	56 mm
Panel cut-out A × B	411 mm × 256 mm
Weight	4.1 kg
Protection type	IP66 (front side), IP20 (rear side)
Operating temperature range	-20 to +60 °C (vertical mounting)
Storage temperature range	-20 to +70 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus, DNV GL
Model (www.exorint.com)	eX715

Delivery address: Mackenrodtstraße 14

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road


East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

Page 5/17

eX721 - Type 705070/1-x-40-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation
Screen size (diagonal)	Approx. 54.6 cm (21.5")
Resolution	1920 × 1080
Number of colors	16M
Brightness (luminance) typ.	300 cd/m ²
Backlight	LED (dimmable)
Interfaces	3 × Ethernet, 2 × USB host, 1 × serial
Voltage supply	DC 24 V (10 to 32 V)
Current consumption	1.7 A at DC 24 V
Installation type	Installation in panel cut-out
Dimensions L × H × (D + T)	552 mm × 347 mm × (56 + 8.5) mm
Front panel depth T	8.5 mm
Mounting depth D	56 mm
Panel cut-out A × B	541 mm × 336 mm
Weight	6.1 kg
Protection type	IP66 (front side), IP20 (rear side)
Operating temperature range	-20 to +60 °C (vertical mounting)
Storage temperature range	-20 to +70 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus, DNV GL
Model (www.exorint.com)	eX721

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 +44 1279 62 50 29

Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6733 Myers Road


East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

EXOR Food & Beverage eXFB

eX707FB - Type 705070/2-x-11-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation
Screen size (diagonal)	Approx. 17.8 cm (7")
Resolution	800 × 480
Number of colors	16M
Brightness (luminance) typ.	500 cd/m ²
Backlight	LED (dimmable)
Interfaces	3 × Ethernet, 2 × USB host, 1 × serial
Voltage supply	DC 24 V (10 to 32 V)
Current consumption	0.7 A at DC 24 V
Installation type	Installation in panel cut-out
Dimensions L × H × (D + T)	217 mm × 177 mm × (45 + 10) mm
Front panel depth T	10 mm
Mounting depth D	45 mm
Panel cut-out A × B	176 mm × 136 mm
Weight	2.5 kg
Protection type	At the front IP69, at the rear IP20
Operating temperature range	-20 to +60 °C (vertical mounting)
Storage temperature range	-20 to +70 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus
Model (www.exorint.com)	eX707FB

Delivery address: Mackenrodtstraße 14

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road


East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

Page 7/17

eX715FB - Type 705070/2-x-31-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation
Screen size (diagonal)	Approx. 39.6 cm (15.6")
Resolution	1366 × 768
Number of colors	16M
Brightness (luminance) typ.	400 cd/m ²
Backlight	LED (dimmable)
Interfaces	3 × Ethernet, 2 × USB host, 1 × serial
Voltage supply	DC 24 V (10 to 32 V)
Current consumption	1.2 A at DC 24 V
Installation type	Installation in panel cut-out
Dimensions L × H × (D + T)	450 mm × 295 mm × (56 + 8) mm
Front panel depth T	8 mm
Mounting depth D	56 mm
Panel cut-out A × B	411 mm × 256 mm
Weight	5.2 kg
Protection type	At the front IP69, at the rear IP20
Operating temperature range	-20 to +60 °C (vertical mounting)
Storage temperature range	-30 to +80 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus
Model (www.exorint.com)	eX715FB

Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House

Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.


6733 Myers Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

EXOR JSmart eXJS

eX707JS - Type 705070/3-x-12-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation (also with gloves)
Screen size (diagonal)	Approx. 17.8 cm (7")
Resolution	1024 × 600
Number of colors	16M
Brightness (luminance) typ.	400 cd/m ²
Backlight	LED (dimmable)
Interfaces	1 × Ethernet (PoE), 1 × USB host (adapter required)
Voltage supply	Power over Ethernet (IEEE 802.3af PoE)
Power consumption	9 W
Installation type	Threaded mounting M22
Dimensions without thread	195.2 mm × 131.6 mm × 16.5 mm
Thread length	17 mm
Weight	0.7 kg
Protection type	IP67 (suitable accessories and suitable cables required)
Operating temperature range	-20 to +55 °C (vertical mounting)
Storage temperature range	-30 to +80 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus
Model (www.exorint.com)	JSmart707

Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany 36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk


JUMO Process Control, Inc.

6733 Myers Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

eX710JS - Type 705070/3-x-22-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation (also with gloves)
Screen size (diagonal)	Approx. 25.7 cm (10.1")
Resolution	1280 × 800
Number of colors	16M
Brightness (luminance) typ.	400 cd/m ²
Backlight	LED (dimmable)
Interfaces	1 × Ethernet (PoE), 1 × USB host (adapter required)
Voltage supply	Power over Ethernet (IEEE 802.3af PoE)
Power consumption	12 W
Installation type	Threaded mounting M22
Dimensions without thread	264.5 mm × 183.1 mm × 16.5 mm
Thread length	17 mm
Weight	1.2 kg
Protection type	IP67 (suitable accessories and suitable cables required)
Operating temperature range	-20 to +55 °C (vertical mounting)
Storage temperature range	-30 to +80 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus
Model (www.exorint.com)	JSmart710

Delivery address: Mackenrodtstraße 14

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road East Syracuse, NY 13057, USA


Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

Page 10/17

eX715JS - Type 705070/3-x-32-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation (also with gloves)
Screen size (diagonal)	Approx. 39.6 cm (15.6")
Resolution	1366 × 768
Number of colors	16M
Brightness (luminance) typ.	400 cd/m ²
Backlight	LED (dimmable)
Interfaces	1 × Ethernet (PoE), 1 × USB host (adapter required)
Voltage supply	Power over Ethernet (IEEE 802.3af PoE)
Power consumption	19 W
Installation type	Threaded mounting M22
Dimensions without thread	398.6 mm × 248 mm × 26.5 mm
Thread length	17 mm
Weight	4.0 kg
Protection type	IP67 (suitable accessories and suitable cables required)
Operating temperature range	-20 to +55 °C (vertical mounting)
Storage temperature range	-30 to +80 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus
Model (www.exorint.com)	JSmart715

Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House

Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.


6733 Myers Road East Syracuse, NY 13057, USA

Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

eX721JS - Type 705070/3-x-42-...



Screen type	TFT color screen
Touch technology	Capacitive, multi-touch operation (also with gloves)
Screen size (diagonal)	Approx. 54.6 cm (21.5")
Resolution	1920 × 1080
Number of colors	16M
Brightness (luminance) typ.	400 cd/m ²
Backlight	LED (dimmable)
Interfaces	1 × Ethernet (PoE), 1 × USB host (adapter required)
Voltage supply	Power over Ethernet (IEEE 802.3af PoE)
Power consumption	32 W
Installation type	Threaded mounting M22
Dimensions without thread	534.1 mm × 325.6 mm × 26.5 mm
Thread length	17 mm
Weight	6.0 kg
Protection type	IP67 (suitable accessories and suitable cables required)
Operating temperature range	-20 to +55 °C (vertical mounting)
Storage temperature range	-30 to +80 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus
Model (www.exorint.com)	JSmart721

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6733 Myers Road


East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

EXOR eSMART eXES

eX04ES - Type 705070/4-x-01-...



Screen type	TFT color screen
Touch technology	Resistive
Screen size (diagonal)	Approx. 10.9 cm (4.3")
Resolution	480 × 272
Number of colors	64k
Brightness (luminance) typ.	200 cd/m ²
Backlight	LED (dimmable)
Interfaces	1 × Ethernet, 1 × USB host, 1 × serial
Voltage supply	DC 24 V (10 to 32 V)
Current consumption	0.25 A at DC 24 V
Installation type	Installation in panel cut-out
Dimensions L × H × (D + T)	147 mm × 107 mm × (29 + 5) mm
Front panel depth T	5 mm
Mounting depth D	29 mm
Panel cut-out A × B	136 mm × 96 mm
Weight	Approx. 0.4 kg
Protection type	IP66 (front side), IP20 (rear side)
Operating temperature range	0 to 50 °C (vertical mounting)
Storage temperature range	-20 to +70 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus, DNV GL
Model (www.exorint.com)	eSMART04M

Delivery address: Mackenrodtstraße 14

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road


East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

Page 13/17

eX07ES - Type 705070/4-x-13-...



Screen type	TFT color screen
Touch technology	Resistive
Screen size (diagonal)	Approx. 17.8 cm (7")
Resolution	800 × 480
Number of colors	64k
Brightness (luminance) typ.	200 cd/m ²
Backlight	LED (dimmable)
Interfaces	1 × Ethernet, 1 × USB host, 1 × serial
Voltage supply	DC 24 V (10 to 32 V)
Current consumption	0.3 A at DC 24 V
Installation type	Installation in panel cut-out
Dimensions L × H × (D + T)	187 mm × 147 mm × (29 + 5) mm
Front panel depth T	5 mm
Mounting depth D	29 mm
Panel cut-out A × B	176 mm × 136 mm
Weight	Apprpx. 0.6 kg
Protection type	IP66 (front side), IP20 (rear side)
Operating temperature range	0 to 50 °C (vertical mounting)
Storage temperature range	-20 to +70 °C
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing
Approvals	cULus, DNV GL
Model (www.exorint.com)	eSMART07M

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road


East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

Page 14/17

eX10ES - Type 705070/4-x-23-...



Screen type	TFT color screen						
Touch technology	Resistive						
Screen size (diagonal)	Approx. 25.7 cm (10.1")						
Resolution	1024 × 600						
Number of colors	64k						
Brightness (luminance) typ.	200 cd/m ²						
Backlight	LED (dimmable)						
Interfaces	1 × Ethernet, 1 × USB host, 1 × serial						
Voltage supply	DC 24 V (10 to 32 V)						
Current consumption	0.38 A at DC 24 V						
Installation type	Installation in panel cut-out 282 mm × 197 mm × (29 + 6) mm 6 mm						
Dimensions L × H × (D + T)							
Front panel depth T							
Mounting depth D	29 mm						
Panel cut-out A × B	271 mm × 186 mm						
Weight	Approx. 1.0 kg						
Protection type	IP66 (front side), IP20 (rear side)						
Operating temperature range	0 to 50 °C (vertical mounting)						
Storage temperature range	-20 to +70 °C						
Resistance to climatic conditions	Relative humidity 5 to 85 %, non-condensing						
Approvals	cULus, DNV GL						
Model (www.exorint.com)	eSMART10						

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road

East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com




Data Sheet 705070

Page 15/17

tci

E07A-XI - Type 705070/5-x-14-...



Screen type	TFT color screen Capacitive, multi-touch operation						
Touch technology							
Screen size (diagonal)	Approx. 17.8 cm (7")						
Resolution	1024 × 600 LED 1 × Ethernet, 1 × USB host						
Backlight							
Interfaces							
Voltage supply	DC 24 V						
Installation type	Installation in panel cut-out (or VESA 75 fastening)						
Dimensions	210 mm × 141 mm × 32 mm						
Panel cut-out	163 mm × 97 mm Approx. 0.45 kg						
Weight							
Protection type	At the front IP54, at the rear IP20						
Operating temperature range	0 to 60 °C ^a						
Storage temperature range	0 to 70 °C						
Resistance to climatic conditions	Relative humidity 10 to 90 %, non-condensing						
Approvals	Not available						
Model (www.tci.de)	E07A-XI						

^a Depending on components, cooling concept and equipment.

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk JUMO Process Control, Inc.

6733 Myers Road

East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 705070

Page 16/17

E10A-XI - Type 705070/5-x-24-...



Screen type	TFT color screen Capacitive, multi-touch operation							
Touch technology								
Screen size (diagonal)	Approx. 25.4 cm (10")							
Resolution	1024 × 600							
Backlight	LED							
Interfaces	1 × Ethernet, 1 × USB host, 1 × USB device, 1 × serial							
Voltage supply	DC 24 V							
Installation type	Installation in panel cut-out (or VESA 75 fastening)							
Dimensions	282 mm × 185 mm × 35 mm							
Panel cut-out	260 mm × 163 mm Approx. 1.0 kg							
Weight								
Protection type	At the front IP54, at the rear IP20							
Operating temperature range	0 to 50 °C ^a							
Storage temperature range	0 to 70 °C							
Resistance to climatic conditions	Relative humidity 10 to 90 %, non-condensing							
Approvals	cULus							
Model (www.tci.de)	E10A-XI							

a Depending on components, cooling concept and equipment.

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road
East Syracuse, NY 13057, USA
Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net
Internet: www.jumousa.com



Data Sheet 705070

Page 17/17

Order details

	(1)	Basic type
705070		Web panel with TFT-touchscreen
	(2)	Basic type extension
1		EXOR Standard eX
2		EXOR Food & Beverage eXFB
3		EXOR JSmart eXJS
4		EXOR eSMART eXES
5		tci E-Serie E-XI
	(3)	Version
8		Standard with default settings
	(4)	Screen size (diagonal) ^a
03		4.3" eX04ES
10		7" eX707
11		7" eX707FB
12		7" eX707JS
13		7" eX07ES
14		7" E07A-XI
20		10.1" eX710
22		10.1" eX710JS
23		10.1" eX10ES
24		10" E10A-XI
30		15.6" eX715
31		15.6" eX715FB
32		15.6" eX715JS
40		21.5" eX721
42		21.5" eX721JS
	(5)	Technology ^a
0		Resistive
1		Capacitive
	(6)	Voltage supply ^a
40		IEEE 802.3af PoE
41		DC 24 V
	(7)	Extra codes ^b
000		Without approval
061	·	With UL approval
062		With DNV GL approval

^a The selection options are dependent on the basic type extension.

Order code Order example

(1)		(2)		(3)		(4)		(5)		(6)	
705070	/		-	8	-		-		-		1
705070	1	1	_	8	-	20	-	1	-	36	_

b The extra codes are dependent on the basic type extension and cannot be selected when ordering.