

Cosmos LED-R, 2x9W, 3000K, Transparent, IP44

Item: 7099430

MALMBERGS



Product information

Range of uses

General lighting for indoor and outdoor use. With or without HF sensor.

Mounting

Surface mounting. Fast connection terminal block 3x2.5 mm². Cable inlet through 2x Ø 19 mm holes at the top of the fitting and 2x Ø 19 mm knockout holes, one on each end. Supplied with 4 membrane nipples.

Description

White body made of steel plate and end plates made of polycarbonate. Transparent diffuser made of acrylic. Including LED tubes. Note: Intended for LED tubes only (Retrofit).

Specifications

Colour consistency	3 SDCM
Colour rendering index (CRI)	Ra83
Colour temperature	3000K
Dims (LxWxH)	660x160x63 mm
Energy efficiency class	A++-A
IP rating	IP44
Luminous flux	1592lm
Power	2x9W
Weight	1,5 kg