



Diagonal Cutters

ISO 5749

- the essential cutting tool for versatile use
- high quality material and precise workmanship for long service life
- precision cutting edges (cutting edge hardness approx. 62 HRC) for soft and hard wire
- clean cutting of thin copper wires, also at the cutting edge tips
- narrow head style for use in confined areas
- Vanadium electric steel; forged, oil-hardened



70 01 160




70 02 160




70 08 160 SBA



Cuts fine wires cleanly over the complete length of the blades



The slim head style and precise cutting capability are perfect for working in confined areas



Product Number	↔ inch	↔ mm	Pliers	Head	Handles	Cutting capacities							
						Ø inch	Ø inch	Ø inch	Ø mm	Ø mm	Ø mm	Ounces	
70 01 110	4 1/4	110	black atramentized	polished	plastic coated	1/8	5/64	3/64	3.0	2.0	1.2	2.8	
70 01 125	5	125				1/8	3/32	1/16	3.0	2.3	1.5	2.8	
70 01 140	5 1/2	140				5/32	3/32	5/64	4.0	2.5	1.8	4.4	
70 01 160	6 1/4	160				5/32	7/64	5/64	4.0	2.8	2.0	6.0	
70 01 180	7 1/4	180				5/32	1/8	3/32	4.0	3.0	2.5	7.1	
70 02 125	5	125	black atramentized	polished	with multi-component grips	1/8	3/32	1/16	3.0	2.3	1.5	4.2	
70 02 140	5 1/2	140				5/32	3/32	5/64	4.0	2.5	1.8	5.3	
70 02 160	6 1/4	160				5/32	7/64	5/64	4.0	2.8	2.0	7.3	
70 02 180	7 1/4	180				5/32	1/8	3/32	4.0	3.0	2.5	8.9	
70 08 160 SBA	6 1/4	160	⚠1000V	black atramentized	polished	insulated with multi-component grips, VDE-tested	5/32	7/64	5/64	4.0	2.8	2.0	6.0
70 08 180 SBA	7 1/4	180	5/32				1/8	3/32	4.0	3.0	2.5	7.1	