



73 72 180



PATENTED



TwinForce® – High Performance Diagonal Cutters

The superior High-Leverage Diagonal Cutter with patented double joint

- ideal transmission of force due to double-hinged design
 - reliably cuts all types of wire, including steel tape
 - for rough or very fine cutting
 - low cutting impact: gentle on hands. The tension on muscles and tendons is relieved
 - for comfortable cutting, repetitive cutting or extremely hard cutting jobs
 - high degree of stability and zero-backlash due to precisely milled forged-in axles
 - New for diagonal cutters: The option to reapply the tool. The KNIPEX TwinForce® cuts even 4 mm thick wire without great effort when reapplied two or three times. Conventional high leverage diagonal cutters either cannot cut these diameters or only with very great effort
 - Chrome vanadium heavy-duty steel, forged, oil-hardened
- 73 72 180 F**
- with opening spring to simplify reapplication and for repetitive cutting



Extremely easy cutting
with little strain:
cuts again 50 % easier than the tried and
tested KNIPEX high leverage diagonal cutters



Article No.	EAN 4003773-		Ø mm	Ø mm	Ø mm	Ø mm	↔ mm
73 71 180	074762		5.5	4.6	3.2	3.0	180
73 72 180	074779		5.5	4.6	3.2	3.0	180
73 72 180 F	077657	MM	5.5	4.6	3.2	3.0	180

Magnetic LED Lamp

Strong. Bright. Compact.

- for illuminating dark working areas
- attachment to tool by means of strong magnets
- very compact dimensions
- approx. 24 hours of lighting, with 2 replaceable button cells (CR1220)
- snap-hook fastening
- impact-resistant plastic housing

Article No.	EAN 4003773-
00 11 V50	075387

