

Diagonal Cutters

- the indispensable diagonal cutter for all-round use
- high quality material and precise workmanship for long service life
- precision cutting edges for soft and hard wire
- clean cutting of thin copper wires, also at the cutting-edge tips
- cutting edges additionally induction hardened, cutting edge hardness approx. 62 HRC
- narrow head style for use in confined areas
- Vanadium electric steel; forged, oil-hardened



Article No.	EAN 4003773-		Ø mm	Ø mm	Ø mm	√ → mm
70 06 125	018124	<u>A</u> 1000 V △ 🛋	3.0	2.3	1.5	125
70 06 140	040293	<u></u> 1000 V △ €	4.0	2.5	1.8	140
70 06 160	021995	<u>A</u> 1000 V △	4.0	2.8	2.0	160
70 06 180	033813	☆ 1000 V △	4.0	3.0	2.5	180



Article No.	EAN 4003773-		Ø mm	Ø mm	Ø mm	√ —► mm
74 06 160	040705	≙ 1000 V △	3.4	2.5	2.0	160
74 06 180	022985	≙ 1000 V △	3.8	2.7	2.2	180
74 06 200	033820	≙ 1000 V △	4.2	3.0	2.5	200
74 06 250	041955	☆ 1000 V △	4.6	3.5	3.0	250



High Leverage Diagonal Cutters

- with integrated forged axle for heaviest duty
- high cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- precision cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC

Length 250 mm

• the 250-mm-long diagonal cutter is suitable for copper conductors up to 16 mm² and aluminium conductors up to 35 mm²





THE WORLD OF THE KNIPEX DIAGONAL CUTTERS





