

## LED Filament Series



### VT-1955

#### HIGHLIGHTS :

WATTS



4

EQ. WATTS



35

LUMINOUS



350

BEAM ANGLE



300

Item No	: VT-1955
SKU Code	: 7113
Watts	: 4
EQ Watts	: 35
Base / holder	: E14
Voltage	: AC:220-240V,50Hz
Lumen(lm)	: 350
Color Temperature	: 2200K
Beam Angle	: 300
Commercial type	: CANDLE
PF	: >0.4
LED Chip Type	: FILAMENT
CRI	: >80
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP20

Body type	: GLASS
Dimmable	: No
Life Time	: 20,000 Hours
Operation Temperature	: -20~50'C
EAN code	: 3800157609883
Unit size	: 37mm x 100mm
Packing details	: 100
Unit cbm	: 0.000144

#### PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb

[CLICK HERE](#)  
FOR OTHER RELATED CERTIFICATES