

#### **FEATURES**

- Bourdon tube operating principle
- Dual scale calibrated in bar and psi
- Medium operating temperature +60°C
- Accuracy ±2.5% FSD (EN837-1/6 class 2.5)
- Rear connection with BSP tapered thread

# WIKA 9350569 Analogue Positive Pressure Gauge Back Entry 10bar, Connection Size R 1/8

RS Stock No.: 722-788



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

# **Analogue Positive Pressure Gauges**



### **Product Description**

These Wika pressure gauges are designed on the bourdon tube operating principle. These gauges can be used within small capacity compressors, medical engineering, heating and Air Conditioning applications. Ideal for pneumatic applications. These gauges are reliable and work well monitoring the pressures of gaseous and liquid media (except highly viscous media).

#### **General Specifications**

Pressure Gauge Type	Back Entry
<u> </u>	Dack Entry
Minimum Pressure Measurement	0bar
Best Accuracy	±1.6%
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	60°C
Applications	Pneumatics, heating and air-conditioning technology, small capacity compressors and medical engineering

## **Mechanical Specifications**

Gauge Outside Diameter	40mm
------------------------	------









