

## FEATURES

- Three poles
- Three-phase starter
- Automatic motor starter functionality
- Disconnect switch not included
- DOL motor starter type
- Range available with and without isolator
- Power rating of 7.5kW
- Voltage rating of 230VAC
- Current rating of 13A to 18A

## RS PRO 7.5 kW DOL Starter, 230 V ac, 3 Phase, IP65

RS Stock No.: 725-5516



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Used to reduce the current required when starting up induction motors, the 7.5 kW automatic 3-phase starter is a direct-on-line (DOL) motor starter. This type of starter is typically used with induction motors rated below 5 hp.

## General Specifications

<b>Motor Starter Type</b>	DOL
<b>Motor Starter Functionality</b>	Automatic
<b>Number of Poles</b>	3
<b>Motor Supporting Range</b>	5.5kW to 11kW
<b>Reversibility</b>	No
<b>Enclosure</b>	Yes
<b>Material</b>	Plastic
<b>Additional Features</b>	Disconnect Switch Not Included
<b>Applications</b>	Workshop machinery, large fans and water pumps

## Electrical Specifications

<b>Phase</b>	3
<b>Power Rating</b>	7.5kW
<b>Voltage Rating</b>	230VAC
<b>Current Rating</b>	13A to 18A
<b>Maximum Allowed Motor Current</b>	18A

## Mechanical Specifications

Overall Length	193mm
Overall Width	88mm
Overall Depth	134mm

## Operation Environment Specifications

Operating Temperature	-25°C to 60°C
-----------------------	---------------

## Protection Category

IP Rating	IP65
-----------	------

## Approvals

Compliance/Certifications	CE
Standards Met	RoHS Compliant; IEC/EN 60947-1; IEC/EN 60947-4-1

