

FEATURES

- Three poles
- Three-phase starter
- Automatic motor starter functionality
- Disconnect switch included
- DOL motor starter type
- Range available with and without isolator
- Power rating of 5.5kW
- Voltage rating of 400VAC
- Current rating of 9A to 14A

RS PRO 5.5 kW DOL Starter, 400 V ac, 3 Phase, IP65

RS Stock No.: 725-5529



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The 5.5 kW automatic 3-phase starter is a direct-on-line (DOL) motor starter used to reduce the current required when starting up induction motors. Such starters are particularly handy for use with induction motors rated below 5 hp.

General Specifications

Motor Starter Type	DOL
Motor Starter Functionality	Automatic
Number of Poles	3P
Motor Supporting Range	5.5kW to 11kW
Reversibility	No
Enclosure	Yes
Material	Plastic
Additional Features	Disconnect Switch Included
Applications	Workshop machinery, large fans and water pumps

Electrical Specifications

Phase	3
Power Rating	5.5kW
Voltage Rating	400VAC
Current Rating	9A to 14A
Maximum Allowed Motor Current	14A

Mechanical Specifications

Overall Length	225mm
Overall Width	110mm
Overall Depth	148mm

Operation Environment Specifications

Operating Temperature	-25°C to 60°C
------------------------------	---------------

Protection Category

IP Rating	IP65
------------------	------

Approvals

Compliance/Certifications	CE
Standards Met	RoHS Compliant; IEC/EN 60947-1; IEC/EN 60947-4-1

