

ENGLISH

Datasheet SPDT PCB ON-ON Push Button Switch

RS Stock number 734-6798



Specifications:


Mechanical Life: Contact Resistance:

Insulation Resistance: Dielectric Strength: Operating Temperature: Case: Plunger: Bushing: Housing: Terminal/Contact: RoHS: Rating: 50,000 make-and-break cycles 50m Ω max. Initial @ 2-4V DC, 100mA for both silver and gold plated 1,000MΩ min. 1,000Vrms @ sea level -30°C to 85°C Diallyl phthalate (DAP) (UL94V-0) Glass filled nylon or glass filled polyester Brass, nickel plated Stainless Steel Silver or gold plated 2002/95/EC R: 0.4VA max. @ 20V max. (AC or DC) Q: 1A @ 250VAC 3A @ 120VAC or 28VDC



ENGLISH

Dimensions – inch mm



PANEL MOUNTING

Model No.	POS,1	POS,2
	Å	â
7MS7	ON	MOM
Term.		
Comm.	1-3	1-2
SCHEMATIC	1 Comm.	1 Comm. 0

SWITCH FUNCTION

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.