

FEATURES

- Ergonomic multi-component handles
- Optimum balance of torque and control
- High quality
- VDE approved
- Chrome Vanadium Steel

RS PRO 88 Piece Electricians Tool Kit with Case, VDE Approved

RS Stock No.: 734-8885



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing the RS Pro 88 piece electricians tool kit, an extensive kit offering various tools to carry out a range of tasks for the serious DIY enthusiast or professional user. The RS PRO 88 piece electricians tool kit is designed for professional engineers who work on or around electrically live circuits.

General Specifications

Set Type	Electricians
Set Contents	Bits, Cutters, Hammer, Hex Keys, Pliers, Ratchet, Screwdriver, Sockets, Tape Measure, Voltage Tester
Number of Pieces	88
Storage Type	Case
Applications	Electrician, Home use
Shelf life	Three years

Mechanical Specifications

Tool Case Dimension	470mm x 370mm x 85mm
----------------------------	----------------------

Kit Contains

Name	QTY
1/2" DR metric hex sleeves 14mm, 15mm, 16mm, 17mm, 18mm, 19mm, 20mm, 21mm, 22mm, 23mm, 24mm, 27mm, 30mm, 32mm	14
1/2" DR extension rod 125mm & 250mm	2
1/2" DR hexagonal plug wrench 16mm & 21mm	2
1/2" DR reversible ratchet wrench	1
1/2" DR universal joint	1
1/2" DR Sliding T head	1
1/4" DR metric Hex Socket 4mm, 4.5mm, 5mm, 5.5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm	12
1/4" DR extension rod 55mm & 100mm	2
1/4" DR connector	1
1/4" DR reversible ratchet wrench	1
1/4" DR universal joint	1
1/4" DR T-type slider	1
metric ribbed wrench 8mm, 10mm, 12mm, 13mm, 14mm, 17mm	6
6" insulated slip-joint pliers	1
6" insulated nipper pliers 6"	1
7" insulated wire cutter	1
6" insulated wire stripper	1
Electrician shears	1
1-120-250V test pencil	1
Insulated Water pump pliers	2
300G brick hammer	1
knob	1
1-5 m tape measure	2
hexagonal plate 1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm	9
1/4" batch head 25MM (L) Phillips: #0, #1, #2, #3, Pozidriv cross: #0,#1,#2,#3, Torx: T20, T25, T30, T40 Slotted: 3-4-5.5-6mm, Hexagon: 3-4-5-6mm	20
Double-color insulated slotted screwdriver: 2.5X 0.4X80MM, 3.5X0.6X100MM, 5.5X1.0X125MM	5
Phillips screwdriver:#0X75MM, #1X 100MM	

Approvals

VDE/1000V Approved	Yes
--------------------	-----

