





Datasheet

Finger Guard 120mm Steel

RS Stock number 737-3998

Dimensions: (mm)





Specification

G109-15A

WIRE DIAMETER.
RING DIA: 1.8mm
RIB DIA: 1.8mm

FINISH: BRIGHT NICKEL CHROME

PART NO. G109-15A/PK

10-PACK G109-15A GUARDS, BOXED

G109-15AB

WIRE DIAMETER. RING DIA: 1.8mm RIB DIA: 1.8mm FINISH: BLACK

PART NO. G109-15AB/PK

10-PACK G109-15AB GUARDS, BOXED

NOTES

- 1. MATERIAL: C1008 BRIGHT BASIC WIRE
- 2. WELD JOINTS TO WITHSTAND 88LBS PULL FORCE
- 3. GENERAL TOLERANCE UNLESS NOTED +/0.5mm
- 4. PART MEETS 6.35mm PLUG GAUGE TEST

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.