




Datasheet

Finger Guard 172mm Steel

RS Stock number 737-4014

Dimensions: (mm)





Specification

G172-10HA

WIRE DIAMETER RING DIA: 1.8mm RIB DIA: 2.3mm

FINISH: BRIGHT NICKEL CHROME

PART NO. G172-10HA/PK

10-PACK G172-10H GUARDS, BOXED

PG172-10HAB

WIRE DIAMETER RING DIA: 1.8mm RIB DIA: 2.3mm FINISH: BLACK

PART NO. G172-10HAB/PK

10-PACK G172-10HAB GUARDS,

BOXED

NOTES:

1. MATERIAL: C1008 BRIGHT BASIC WIRE

2. WELD JOINTS TO WITHSTAND 88LBS PULL FORCE

3. GENERAL TOLER-ANCE UNLESS NOTED +/-0.5mm

4. PART MEETS 6.35mm PLUG GAUGE TEST

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.