

Features

- Standard height: 350mm Standard
- Diameter: 182mm
- Inlet & outlet: 1" female.
- Max working pressure: 8 bar

RS PRO Stainless Steel Single Non Return Valve 1/2 in BSP

RS Stock No.: 738-2700



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Check Valves



Product Description

Introducing the RS PRO DWFK-CALMAX water filter housing kit an ideal way to introduce fresh quality tasting drinking water to everyday life, removing murky looking and poor tasting water. Even tap water that is safe to drink can contain particles and contaminants. The unit is a one off investment as you can buy replacement cartridges that is easily removable from the water filter housing unit. To be used with a 10 high flow filter cartridge – see 738-2703 or 738-2706. Typical users of the heavier housing unit are farms, offices & factories.

General Specifications

Filter Element	Cartridge
Colour	Black/Blue
Maximum Flow Without Cartridge	60L/min
Thread Size	1/2in
Inlet & Outlet Connection	1in BSP
Maximum Working Pressure	8bar
Inlet & Outlet Size	1in
Inlet & Outlet Thread Standard	BSP

