

#### **FEATURES**

- Gold plated contacts
- Beryllium copper contacts
- 23.1mm long
- Various plug types offered in this range of coaxial adapters
- Straight and rightangle body offered in this range

# Straight 50Ω RF Adapter MCX Plug to SMA Socket 6GHz

RS Stock No.: 738-5819



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

From RS PRO comes a range of high quality and great value coaxial adapters, These coaxial type adapters have been designed to provide an effective method of connecting coaxial cable assemblies through a panel mounting connection. Manufactured out of industry standard components, these connectors are most commonly used for connecting radio and television broadcast equipment.

#### **General Specifications**

Adapter Type	MCX Plug to SMA Socket
Adapter Type A	MCX
Adapter Type B	SMA
Gender A	Plug
Gender B	Socket
Body Orientation	Straight
Contact Plating	Gold
Body Plating	Gold
Contact Material	Beryllium Copper
Insulation Material	PTFE
Body Material	Brass
Centre contact Material	Beryllium Copper
Chassis Material	Beryllium Copper
Body Finish	Gold 3µ" min
Centre Contact Finish	Gold 50µ" min
Chassis Finish	Gold 3µ" min
Application	Test and measurement, Communication systems, GPS equipment, Antennas



# **Electrical Specifications**

Impedance	50 Ω
Operating Frequency	6GHz
Voltage Rating	335 V
VSWR	1.3 Max

### **Mechanical Specifications**

Length	23.1 mm
Length	23.1 11111
1	

# **Operation Environment Specifications**

Operating Temperature	-55°C to +155°C
-----------------------	-----------------

# **Approvals**

Compliance/Certifications	2011/65/EU and 2015/863
---------------------------	-------------------------

