



ENGLISH

Datasheet

Straight Die Grinder

6mm Die Grinder

[RS Stock No. 739-8398](#)



Specifications:

Power Source	: Compressed air
Maximum permissible operating pressure	: 90 psi (6.2 bar)
Recommended operating pressure	: 90 psi (6.2 bar)
Material	: Aluminium
Size	: 6mm Collet
Free Speed	: 22,000RPM
Weight	: 0.6kgs / 1.37lbs Length: 6.9" / 175mm
Min Hose Size	: 10mm Air inlet thread: 1/4"
Sound	: 93dBA Vibration: 5.4m/s ²
Ave Air Consumption	: 3cfm / 85 l/min
Recommended lubrications	: 10 Weight SAE Oil

Features :

- Medium motor size
- 6mm collet (3 piece design)
- Rear exhaust through handle
- High velocity, low vibration
- Safety throttle lever
- Positive throttle action
- Very versatile, excellent in confined workspace