

FEATURES

- **Magnetic lock**
- **Z and L bracket - for inward opening door, simple fitting**
- **Power consumption: DC 12V-15V, Current 150mA**
- **RF Frequency: 125KHz**
- **With internal EM reader**
- **Unlock output delay time: 0s – 99s**
- **Output: 1 relay**
- **Relay rating: 2A/12Vdc**
- **Read range: 5cm to 10cm**
- **Infrared keypad operation**
- **Built-in anti-tamper**

RS PRO Door Entry including Access Control Kit

RS Stock No.: 741-8234



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO access control kit is an ideal device that can be used in a range of environments or applications, especially in areas where the management of people flow, traffic and security need to be monitored, especially on entry and exit points of buildings like shops, offices, schools and much more.

General Specifications

System Type	Access Control Kit
Components Included	Break Glass Box, Exit Button, Power Supply, RFID Tokens
Keypad	Infrared keypad operation
Exit button input	Yes
Fitting	simple fitting
Applications	Schools, universities and colleges, Factories and industrial manufacturing, Hospitals and healthcare environments such as research, laboratories, Supermarkets and shops, Offices

Electrical Specifications

Supply Voltage	12V
Consumption current	150mA

Mechanical Specifications

Dimensions	140mm x 220mm x 74mm
Depth	74mm
Height	140mm
Width	220mm
Read Range	5mm to 10mm

Protection Category

IP Rating	IP67
------------------	------

Approvals

Compliance/Certifications	RoHS
----------------------------------	------

Kit Contains:

- 1 x proximity system, 2000 users - Weather resistant, rating IP67
- 1 x 12Vdc, 1Amp boxed power supply
- 1 x magnetic lock
- 1 x Z&L bracket
- 1 x exit button
- 1 x break-glass unit
- 10 x proximity tokens
- 1 x Infrared Controller

