

PNOZ s7 24VDC 4 n/o 1 n/c

750107



## Technical details

Approvals:	CE;cULus Listed;TÜV;KOSHA;CCC
Application options:	Instantaneous contact expansion
Supply voltage (V):	24,0
Max. current at DC1:	6.0 A
Voltage at AC1:	240 V
Terminal type:	Screw terminal
Terminal style:	Plug-in
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Operating modes:	Single-channel;without detection of shorts across contacts
Number of instantaneous safety contacts:	4
Width dimension:	17.5 mm
Height dimension:	98.0 mm
Depth dimension:	120.0 mm
Gross weight:	180 g
Net weight:	170 g
Ambient temperature:	-10 - 55 °C