

PNOZ s6.1 24VDC 3 n/o 1 n/c

750126



## Technical details

Approvals:	CE;cULus Listed;TÜV;KOSHA;CCC
Application options:	Two-hand monitoring Type III A;Simultaneity monitoring
Max. current at DC1:	6.0 A
Voltage at AC1:	240 V
Terminal type:	Screw terminal
Terminal style:	Plug-in
Stop category:	0
Standards:	EN 574 TYP III A;EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Operating modes:	Dual-channel;Detection of shorts across contacts
Supply voltage (V):	24,0
Width dimension:	22.5 mm
Height dimension:	98.0 mm
Depth dimension:	120.0 mm
Gross weight:	195 g
Net weight:	185 g
Ambient temperature:	-10 - 55 °C