

FEATURES

- Material: Stainless steel
- IP69K rating
- Lockable
- Double lipped edge to ensure higher strength and ease of installation
- Easy to use, including removal of the door

RS PRO Wall Boxes - 316 Stainless Steel Wall Box

RS Stock No.: 7587037



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Wall Boxes





RS Pro IP69K Steel Wall Boxes

Brought to you by RS Pro, a range of lockable steel wall mounted enclosures. Rated at IP69K, the level of protection provided by these boxes ensures the contents will be safely stored and protected. The door of the enclosure has a pull out hinge which allows it to be removed for easy access and due to the protection benefit, these wall boxes are suitable for various applications. All models are highly reliable and excellent quality.

General Specifications

Body Material	316 Stainless Steel			
Number Of Doors	1			
Colour	Unpainted			
Gland Plate	No			
Door Lock Type	Кеу			
Chassis Plate	No			
Transparent Door	No			
Fixing Kit	No			
Application	Electrical			
External Mounting Type	Bracket			
Internal Mounting Type	Panel			
Special Features	Double Lip Edges, Dust & Water Protection			

Mechanical Specifications

External Height	300 mm
External Depth	200 mm
External Width	400 mm
Dimensions	300 mm x 200 mm x 400 mm
Weight	10.93 kg

Protection Category

IP Rating	IP69K

Wall Boxes



Approvals	
Declarations	RoHS Certificate of Compliance

Similar Products

Stock No.	Brand	Product Name	Colour	Body Material	Dimensions
758-7006	RS PRO	304 Stainless Steel Wall Box	Unpainted	304 Stainless Steel	300 mm x 200 mm x 400 mm
758-7009	RS PRO	304 Stainless Steel Wall Box	Unpainted	304 Stainless Steel	400 mm x 200 mm x 400 mm