

## FEATURES

- Operating temperature -20°C to +110°C
- Multiple DIN rail fixing points, M5
- External M6 earthing stud
- Double lipped edges
- Manufactured from stainless steel offering excellent durability and corrosion resistance
- IP66 rating offering excellent weatherproof protection
- Suitable for a wide range of applications indoors and outdoors

# RS PRO Wall Boxes - 304 Stainless Steel Wall Box

RS Stock No.: 7586977



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO IP66 Stainless Steel Junction Box, Unpainted

Introducing stainless steel junction boxes from RS PRO, a range of high quality and durable terminal box enclosures for housing DIN rail terminals and accessories in a range of electrical applications. With multiple DIN rail fixing points included, these junction boxes are perfect for installing and protecting electrical wires, connectors and cables, as well as providing a protective case for switches and more.

These junction boxes are manufactured from stainless steel, offering a highly durable and sturdy enclosure that can be installed in a wide range of environments. The terminal boxes feature an IP66 rating, offering excellent weatherproof protection making them ideal for use both indoors and outdoors. These RS PRO stainless steel terminal boxes also feature a wide operating temperature of -20 to +110°C making them highly versatile, allowing them to be used in environments with varied temperatures.

## General Specifications

<b>Body Material</b>	304 Stainless Steel
<b>Number Of Doors</b>	1
<b>Colour</b>	Unpainted
<b>Gland Plate</b>	No
<b>Door Lock Type</b>	Quick Release Lock
<b>Chassis Plate</b>	Yes
<b>Transparent Door</b>	No
<b>Fixing Kit</b>	No
<b>Application</b>	Electrical
<b>External Mounting Type</b>	Bracket
<b>Internal Mounting Type</b>	Perforated Rail
<b>Special Features</b>	Double Lip Edges
<b>For Protection Of</b>	Sensitive electrical equipment

## Mechanical Specifications

<b>External Height</b>	200 mm
<b>External Depth</b>	120 mm
<b>External Width</b>	300 mm
<b>Dimensions</b>	H.200 mm x W.300 mm x D.120 mm
<b>Weight</b>	4.11

## Protection Category

<b>IP Rating</b>	IP66
------------------	------

### Approvals

<b>Declarations</b>	RoHS Certificate of Compliance
---------------------	--------------------------------

### Similar Products

Stock No.	Brand	Product Name	Colour	Body Material	Dimensions
758-6974	RS PRO	304 Stainless Steel Wall Box	Unpainted	304 Stainless Steel	400 mm x 300 mm x 150 mm
758-6970	RS PRO	304 Stainless Steel Wall Box	Unpainted	304 Stainless Steel	1000 mm x 800 mm x 300 mm