

Distribution connector; 1 x plug / 3 x socket; 3-pole; 100% protected against mismating; pluggable; 3-way

Item No.: 770-607



Distribution connector; 1 x plug / 3 x socket; 3-pole; 100% protected against mismating; pluggable; 3-way

Marking

RoHS ✓ Compliant

Business data		
Supplier	WAGO	
Item no.	770-607	
GTIN / EAN	4045454251352	
Content	1	
Order amount	50	
Customer item number		

Notes

Hinweis:Note:All connectors for fixed installations (snap-in versions for lighting fixtures or devices, female locking latch all types of PCB and distribution connectors) are factory-equipped with locking levers to ensure plugs and sockets are securely locked. Additional locking levers are only required for "flying leads" (plug/socket).All WINSTA® components are 100% protected against mismating in terms of:a.) plugging different number of polesb.) plugging when turned by 180°c.) plugging when laterally staggeredd.) plugging one poleNote on Continuous Service Temperature:-35°C ... +85°CPVC cable for temperatures 70 °C (including halogen-free)Insulating parts for temperatures 105 °CMating cycles: 100, with resistive load IN = 25A, tested (4 mm2/AWG 12)

Technical data

Miscellaneous

Printview: Distribution connector; $1 \times plug / 3 \times socket$; 3-pole; 100% protected against mismating;

pluggable; 3-way - Item No.: 770-607

Technical data		
No. of poles	3	
Pin spacing	10 mm (0.394 in)	
Total number of potentials	3	
Potential marking	L ⏚ N	
Color	black	
Coding	A	
Rated voltage (III / 3) [V]	250 [V]	
Rated impulse voltage (III / 3) [kV]	4 [kV]	
Pollution degree (1)	3	
Rated current [A]	25 [A]	
Legend for ratings	(III / 3) Overvoltage category III /	
Mating cycles	200, without resistive load	
Mating force of a plug-in connection	approx. 20 70 N (depending on pole number)	
Unmating force of a plug-in connection	when unlocked: approx. 20 70 N (depending on pole number)	
Retention force of a plug-in connection	when locked: > 80N	
Insulating material	Polyamide 66 (PA 66)	
Flammability class per UL94	VO	
Contact material	Copper or copper alloy, surface-treated	
Processing temperature	-5°C +40°C	
Fire load [MJ]	0.423 [MJ]	
Weight [g]	25.1 [g]	
Width	30 mm / 1.181 Inch	
Height	32.7 mm / 1.287 lnch	
Depth	46 mm / 1.811 Inch	
Marking	L ⏚ N	


pluggable; 3-way - Item No.: 770-607

Images & drawings



Printview: Distribution connector; 1 x plug / 3 x socket; 3-pole; 100% protected against mismating;

pluggable; 3-way - Item No.: 770-607



Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Telefon: 0571/887-0 Fax: 0571/887-169 http://www.wago.com

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.