

### **FEATURES**

- Hi-flex adjustable gooseneck
- Double shade design for efficient heat dissipation
- High quality build
- Lightweight for maximum versatility.

# RS PRO LED Machine Light, 100 → 277 V ac, 3 W, Flexible Neck, 520mm Arm Length

RS Stock No.: 777-7959



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## **Machine Lights**



#### **Product Description**

From RS Pro, this flexible LED work light gives you light where you need it while keeping your hands free. With a fully adjustable gooseneck, there's no lighting angle that can't be achieved. The gooseneck is also vibration resistant, meaning it can be used with confidence in heavy-machinery environments.

#### **General Specifications**

Lamp Type	LED
Light Style	Flexible Arm
Lamp Supplied	Yes
Integral transformer	Yes
Shield Fitted	No
Switch Fitted	No
Shade	Plastic
Neck Length	500mm
Arm Type	Flexible Neck

#### **Electrical Specifications**

Mains Plug Type	Type C - Euro plug
Voltage Rating	100V to 240V
Wattage	3W
EU Energy Efficiency Rating	A+
Number of Bulbs	3

#### **Mechanical Specifications**

Arm Length	520mm
Cable Length	1.8m
Beam Angle	30°



### **Protection Category**

IP Rating	IP 20
IF Ralling	IF 20

## Approvals

Compliance/Certifications RoHS Certificate of Compliance, CE Approved
---









