

#### **FEATURES**

- 30" Long
- Emits a bright, white light at 2860 Lumens
- In built LED driver
- Reinforced Lens for high crack-resistance
- Aluminium body also functions as a heat sink

# RS PRO LED Machine Light, 100 → 260 V ac, 40 W

RS Stock No.: 777-7968



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## **Machine Lights**



#### **Product Description**

From RS Pro, this fixed LED strip light is delivers effective lighting, minimizing eye strain where high concentration tasks and detailed work is taking place. They can be positioned at machines or work places to give excellent illumination exactly where it is needed.

#### **General Specifications**

Lamp Type	LED
Light Style	Linear Fixed
Lamp Supplied	Yes
Integral transformer	Yes
Shield Fitted	No
Switch Fitted	No
service life	up to 40,000hours

#### **Electrical Specifications**

Mains Plug Type	Type C – Euro plug
Voltage Rating	100VAC to 260VAC
Wattage	40W
EU Energy Efficiency Rating	A+
Number of Bulbs	22
Colour Temperature	5000K

#### **Mechanical Specifications**

Length	877mm
Cable Length	1.8m
Beam Angle	80°

#### **Operation Environment Specifications**

Temperature Range	-22°C to 140°C
-------------------	----------------




### **Protection Category**

IP Rating	IP 65

## Approvals

Compliance/Certifications	RoHS Certificate of Compliance, CE Approved
	· · · · · · · · · · · · · · · · · · ·

#### Diagram:



#### RS Article No.:

MODEL	DESCRIPTION	Α	В	С
777-7956	100V~240V, 1Wx6pcs 80°, EU plug	298mm	340mm	332mm
777-8000	100V~240V, 1Wx6pcs 80°, UKplug	298mm	340mm	332mm
777-7965	100V~240V, 1Wx12pcs 80°, EU plug	480mm	522mm	514mm
777-8019	100V~240V, 1Wx12pcs 80°, UK plug	480mm	522mm	514mm
777-7968	100V~240V, 1Wx22pcs 80°, EU plug	835mm	877mm	869mm
777-8012	100V~240V, 1Wx22pcs 80°, UK plug	835mm	877mm	869mm

## Machine Lights

