

Data sheet

Mechanical/Spring Return function, panel/body-mounted spool valve body for M5 valves.



Technical Data

- Maximum Operating Temperature: +50°C
- Minimum Operating Temperature: -10°C
- Maximum Flow: 125 lpm
- Pressure Range: -0.9 to 1 bar

RS Stock Number : 784-0050
Spool Valve Body M5, 3/2
14 N Actuation Force