




Datasheet

RS PRO DC FAN 80x25mm

Stock Number: 787-4016

EN



Frame	PBT UL94 V-0 Plastic	<u>Operating Temperature</u> -10°C ~ +70°C	
Impeller	PBT UL94 V-0 Plastic	<u>Storage Temperature</u> -40°C ~ +70°C	
Connection	2x Wire Leads, 24 AWG	<u>Life Expectancy</u> 40,000 hours (L10 at 40°C)	
Motor	Brushless DC, Auto Cutoff, Auto Restart	Weight: 0.086Kgs (0.19 lbs)	
Bearing System	Sealed Sleeve		
Dielectric Strength	500VAC/min < 1mA		
Insulation Resistance	10M ohm between leadwire and frame (500VDC)		

Model Number	787-4016
Rated Voltage	24 VDC
Rated Power	2.16 W
Rated Current	0.09 A
Rated Speed (RPM)	2000
Airflow (CFM)	25.75
Noise Level (dB)	22.7
Max. Static Pressure	0.07" H ₂ O