

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0795405067](#)  
**Status:** **Active**  
**Overview:** [In-Vehicle Smart Charging Modules](#)  
**Description:** In-Vehicle Dual Port Smart Charger, USB Type A and C, with Backlight, 3.0A USB-C / 2.4A USB-A

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Datasheet \(PDF\)](#)

**General**

Product Family	I/O Connectors
Series	<a href="#">79540</a>
Application	Module-to-Wire
Component Type	USB Charger
Datasheet Order No	987651-6673
Overview	<a href="#">In-Vehicle Smart Charging Modules</a>
Product Name	Mini50, USB
Type	A, C
UPC	191128872768

**Physical**

Circuits (Loaded)	2
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	10000
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	ABS, PC
Net Weight	43.431/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Ports	2
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	N/A

**Electrical**

Current - Maximum per Contact	2.4A, 3.0A
-------------------------------	------------

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	795405067-000
---------------	---------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 7(a),7(c)-1,6(c)\***

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from product compliance status evaluation.
CUST_NOTE2	50 Image
China ROHS	Not Relevant
ELV	Not Contained*
RoHS Phthalates	

**Search Parts in this Series**

[79540 Series](#)

**Mates With**

USB Type A and USB Type C (Front)<br>Mini50 Unsealed Receptacle 34791-0040 (Rear)

**Use With**

16V DC