

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0797580004](#)  
**Status:** **Active**  
**Overview:** [Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female Gold Plated, 150mm, 20 AWG

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">79758</a>
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Fit 3.0 Crimp Terminals
Overview	<a href="#">Pre-Crimped Leads</a>
Product Name	Micro-Fit 3.0
UPC	884982052673

**Physical**

Cable Length	0.15m
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	1.049/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	20
Wire/Cable Type	UL 1061

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-797580001
---------------	--------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[79758 Series](#)

**Use With**

Micro-Fit 3.0 Receptacle Housings [43645](#), [43025](#), Micro-Fit BMI Panel Mount Housings [44133](#), [44300](#)