

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0797581005](#)
Status: **Active**
Overview: [Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Pico-Lock Female-to-Pico-Lock Female, 150mm, 30 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|-----------------------------------|
| Product Family | Cable Assemblies |
| Series | 79758 |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | Pico-Lock Crimp Terminals |
| Overview | Pre-Crimped Leads |
| Product Name | Pico-Lock |
| UPC | 889056818551 |

Physical

| | |
|------------------------------|----------------------|
| Cable Length | 0.15m |
| Circuits (Loaded) | 1 |
| Color - Resin | Black |
| Gender | Female-Female |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Net Weight | 0.656/g |
| Packaging Type | Bag |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Size AWG | 30 |
| Wire/Cable Type | UL 1061 |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2012341212-000 |
|---------------|----------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[79758 Series](#)

Use With

1.50mm Pitch Pico-Lock Crimp Housing
[504051](#)