

BaiSpot LED PAR16 GU10 5W 3000K 26D Glass Dimm

Article number 80100040596

BAI BaiSpot LED PAR16 GU10 5W 3000K 26D Glass Reflector 380lm Dimmable 240V 50x53mm LED-lamp



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	BaiSpot LED PAR16 GU10 5W 3000K 26D Glass Dimm
Brand	Bailey
Productseries	BaiSpot LED
Product type	BS GU10 Glass
GTIN	08714681405963
Manufacturer articlenumber	80100040596

ETIM specifications

Nominal voltage [V]	220 - 240
Nominal current [mA]	23 - 23
Power factor	0.9
Lamp power [W]	5 - 5
Voltage type	AC
Luminous flux [lm]	380 - 380
Lamp efficacy [lm/W]	76
Colour rendering index CRI	80-89
Lamp shape	Reflector
Filament lamp	No
Type of glass/cover	Clear
Colour of light acc. EN 12464-1	Warm white <3300 K
Socket	GU10
Colour	White
Colour of light	830 - 830
Colour temperature [K]	3000 - 3000
Colour housing	Other
Beam angle [°]	26
Colour consistency (McAdam ellipse)	Other
Dimmable	Yes
Diameter [mm]	50
Length [mm]	53
Degree of protection (IP)	IP20
Lamp designation	PAR16
Energy efficiency class	A
Min. number of switching cycles	50000
Weighted energy consumption in 1,000 hours[kWh]	5