



JUNCTION BOX

Abox 025-L



Abox 025-L

Junction box

CUSTOMIZE

80 x 80 x 52 mm
Article number: 80290701

Junction box acc. to DIN EN 60670 (VDE 0606), $U_i=690V$, with self-sealing, soft inlet membranes, M20, seal range 2 - 16 mm

Grey, without terminal



Technical data

Measures

Width:	80 mm
Length:	80 mm
Height:	52 mm

Material:

Cover:	polystyrene
material:	polystyrene
Box:	polystyrole, membrane out of TPE
Cover screw:	stainless steel V2A

Entries

Pre-embossings, top:	2 x M20
Pre-embossings, left/right:	2 x M20
Pre-embossings, bottom:	1 x M20
Pre-embossings, rear side:	1 x M20

Certificates



Accessory

Abox 025/040 KLS-2,5²/4² - Terminal block

DMS M20/w - M20, white

BST M20/sw - Ventilation seal

Abox PST - Sealing kit

AST M20 - Attachment bushes

BST M20 - Ventilation seal

DMS M20 - Double-membrane seals

KS M20 - Combi set

KVR M20-GDB/MGM - Cable gland

KVR M20-MGM - Cable gland

MPS-KRI - Mounting plate

RST M20 - Conduit connector

SNI M20 - Stepped nipple



JUNCTION BOX

Abox 025-L

Other attributes

Entries:	8
Rated cross section:	2,5 mm ²
Tackable:	No
Rated insulation voltage AC:	690 V
Functional integrity:	none
sealable:	Yes
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP65 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No
Combustion behaviour acc. to UL 94:	HB acc. UL94
Combustion behaviour acc. to VDE:	650°C acc. VDE 0471/ EN 60695
Equipment:	None
Color:	Grey
Cover screw torque:	1 N m

VST M20 - Sealing plugs

WNI M20 - Twist nipple

WST M20 - Twist plug

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%