



JUNCTION BOX

# Abox 060-6<sup>2</sup>



## Abox 060-6<sup>2</sup>

Junction box

**CUSTOMIZE**

110 x 110 x 67 mm  
Article number: 80640701

Junction box acc. to DIN EN 60670 (VDE 0606), Ui=690V, with IP54 attachment bushes, M25, seal range 9 - 18.5 mm, with blanking plug M25

Grey, with high-set screw terminal, 5-pole - 6 mm<sup>2</sup> (4 x 2.5<sup>2</sup> / 4 x 4<sup>2</sup> / 3 x 6<sup>2</sup>)



## Technical data

### Measures

Width:	110 mm
Length:	110 mm
Height:	67 mm

### Material:

Cover:	polystyrene
Box:	polystyrene
material:	polystyrene
Cover screw:	stainless steel V2A

## Certificates



## Accessory

- \_\_\_\_\_ DMS M20/w - M20, white
- \_\_\_\_\_ DMS M25/w - {M 25, weiss}
- \_\_\_\_\_ Abox 060 KLS-6<sup>2</sup> - Terminal block
- \_\_\_\_\_ KS M25-gro - Combi set
- \_\_\_\_\_ BST M20/sw - Ventilation seal
- \_\_\_\_\_ Abox 060 MPI - Mounting plate
- \_\_\_\_\_ Abox PST - Sealing kit
- \_\_\_\_\_ AST M20 - Attachment bushes
- \_\_\_\_\_ AST M25 - Attachment bushes
- \_\_\_\_\_ BST M20 - Ventilation seal
- \_\_\_\_\_ DMS M20 - Double-membrane seals
- \_\_\_\_\_ DMS M20/sw - Double-membrane seals
- \_\_\_\_\_ DMS M25 - Double-membrane seals



JUNCTION BOX

# Abox 060-6<sup>2</sup>

## Other attributes

Entries:	9
Rated cross section:	6 mm <sup>2</sup>
Tackable:	No
Rated insulation voltage AC:	690 V
Explosion safety:	none
Functional integrity:	none
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP65 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No
Combustion behaviour acc. to UL 94:	HB acc. UL94
Combustion behaviour acc. to VDE:	650°C acc. VDE 0471/ EN 60695
Equipment:	Terminal
Color:	Grey
Cover screw torque:	1 N m

GMU PA M20 - Lock nut

GMU PA M25 - Lock nut

KS M20 - Combi set

## Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%