



JUNCTION BOX

# Abox m 025-L



## Abox m 025-L

Junction box

**CUSTOMIZE**

82 x 82 x 52 mm  
Article number: 80790701

Junction box acc. to DIN EN 60670 (VDE 0606),  $U_i=690V$ , with knock-outs, M20, with IP54 attachment bushes, with blanking plug M20, seal range 8 - 13.5 mm

Grey, without terminal



## Technical data

### Measures

Width:	82 mm
Length:	82 mm
Height:	52 mm

### Material:

Cover:	polystyrene
Sealing:	thermoplastic elastomer
material:	polystyrene
Box:	polystyrene
Cover screw:	stainless steel V2A

## Certificates



## Accessory

- Abox PST - Sealing kit
- BST M20/sw - Ventilation seal
- Abox 025/040 KLS-2,5²/4² - Terminal block
- KVR M20-GDB/MGM - Cable gland
- KVR M20-MGM - Cable gland
- AST M20 - Attachment bushes
- WST M20 - Twist plug
- WNI M20 - Twist nipple
- VST M20 - Sealing plugs
- BST M20 - Ventilation seal



JUNCTION BOX

# Abox m 025-L

## Entries

Pre-embossings, top:	2 x M20
Pre-embossings, left/right:	2 x M20
Pre-embossings, bottom:	1 x M20
Pre-embossings, rear side:	1 x M20

## Other attributes

Color:	Grey
Entries:	8
Rated cross section:	2,5 mm <sup>2</sup>
Tackable:	No
Rated insulation voltage AC:	690 V
Functional integrity:	none
sealable:	Yes
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Explosion safety:	none
Ingress protection:	IP65 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No
Combustion behaviour acc. to UL 94:	HB acc. UL94
Combustion behaviour acc. to VDE:	650°C acc. VDE 0471/ EN 60695
Cover screw torque:	1 N m

## Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%