

Datasheet

# RS Pro LED Bench Magnifier, 3 dioptre, 5 dioptre, Table Clamp Mount, 8W

RS Stock No: 808-7042



RS Pro offers a great value range of fluorescent and LED daylight magnifier lamps. The range includes, table lamps, long reach and task lamps, headband magnifiers and lightboxes. The RS Pro Long Reach LED Magnifier Lamp offers a 1.5 m cable and 65 mm clamp, ideal for mobile working and can quickly and easily be moved from desk to desk.



## Lens magnification

- 3 dioptre lens 1.75x
- 5 dioptre lens 2.25x



### How does it work?

The fluorescent daylight tubes allow you to view colours accurately anytime day or night, as well as the smaller detail on objects. The tubes provide a consistent shadow free light source, are energy saving and have low heat emission which means that you can work for longer and in comfort.

### Features and Benefits

- Long reach LED magnifier lamp
- 56 white LED light bulbs, only 9 W in total
- Energy efficient
- Bulbs never need replacing
- Shadow free, cool light
- Quality 125 mm (5") removable lens
- 3 dioptres (1.75 x magnification)
- Built-in handle and Sun Protector cap
- Includes table clamp
- EU quality standards
- Energy Consumption: 8kWh/1000h
- Energy Efficiency Class: A+

Attribute	Value
Dioptre	3 dioptre, 5 dioptre
Lens Size	125mm
Magnifier Type	Table Clamp Mount
Lamp Type	LED
Lamp Wattage	8W
Operating Voltage	220 V ac, 240 V ac
Lens Diameter	125mm
Plug Type	Type C - European Plug, Type G - British 3-pin