



Datasheet





An energy efficient LED daylight lamp with glass lens & versatile swivel head, ideal for intricate work **Features:**

- 30 white LED bulbs, only 2w in total
 - o Energy efficient
 - o Bulbs never need replacing
 - o Shadow free, cool light
- Quality 100mm (4") glass lens
 - o 3 dioptre (1.75x magnification)
 - o Built-in close up lens 12 dioptre (4x mag.)
- Ergonomic design with table base & lens cap
- Quality arm ball joints for easy positioning
- Suitable for mobile use

SPECIFICATIONS

VOLTAGES AVAILABLE: 220v – 240v, 50Hz

MAGNIFIER: 100mm (4") diameter; 3 dioptre lens with 12D mini lens

MAGNIFICATION: 1.75x and 4x for mini lens

HEIGHT: 30cm

SUN PROTECTION CAP: YES

LIGHT SPECIFICATION: 30 LEDs (2w) TUBE PROTECTION COVER: YES

CABLE LENGTH: 1.5m

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.