

## **Features**

- Voltage: 250V AC
- Screw-type mounting
- Black / Grey body colour
- Connection Type
  3Pole + Earth
- Socket Type C

## **RS PRO DIN Connector Socket**

RS Stock No.: 811-8229



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## **DIN 43650 Solenoid Connectors**



#### **Product Description**

The RS PRO Type C DIN connector socket secured in place using a simple screw mount fastener and designed for cable mounting. This solenoid valve connector socket as a Type C is the smallest type of DIN valve connector and is sometimes referred to as a sub-micro or micro DIN.

#### **General Specifications**

Connection Type	3Pole + Earth
Mounting Type	Screw-Type
Туре	MEM-Socket (Micro DIN Connector) – Non-illuminated
Socket Type	Type C
Mounting	M3 Screw
Material for Rubber Gasket	Nitril / Silicon
Material Body	Nylon-6-GF
Gland Size	PG-7
Body Colours	Black / Grey
Terminals	Screw-Type

#### **Electrical Specifications**

Rating	6A, 250V AC

#### **Operation Environment Specifications**

Contact Resitance (Initial)	20 m Ohms max.
Permissible Temp. With/Without Load	0°C to 90°C
Insulation Resistance	100 M Ohms min.
H. V. Breakdown Test	2 KV AC For 1 Minute

#### **Mechanical Specifications**

Current Caring Parts	Copper Alloy, Tin plated
----------------------	--------------------------

# **DIN 43650 Solenoid Connectors**



### **Unit mm**

