

# MPP ARCA 3030



Sample image

**Order symbol:** MPP ARCA 3030

**Product nbr:** 8120752

**Description:** Mounting plate perforated (250x250x2 mm - 26x11 mm)

**Remarks:** Galvanized steel. for size 300x300x210

**EAN:** 6418074082732

**Including:**

**El. number:**

- Finland: 3423833
- Denmark:
- Sweden:

MPP 3030 DIM.jpg

<b>Dimensions:</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm:	250	250	2
inch:	9.84	9.84	0.08

**Materials:**

Material:

Base colour:

Cover colour:

Gasket material:

**Rating:**

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation:

Not insulated

Halogen free (DIN/VDE 0472, Part 815):

0

UV resistance:

-

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

C

Klasa NEMA:

**Temperatures:**

Temperature °C (short term)::

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

**Certificates:**