

## **FEATURES**

- Different types of screwlock assemblies for D sub connectors
- Thread size is 4-40 UNC
- Supplied disassembled

# RS PRO Screwlock D Connector

RS Stock No.: 814-039



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



## **Product Description**

RS PRO range of zinc plated screwlock assemblies for use with D-Sub connectors. The screwlock assembly kits in this range consist of three types; Male screwlock assembly which includes two clips and two locking screws. Female screwlock assemblies available in 8 mm thread length or 13 mm thread length which include locking screws, washers and nuts.

829-918 - Male screwlock assembly

814-023 - Female screwlock assembly 8 mm thread length

814-039 - Female screwlock assembly 13 mm thread length

### **General Specifications**

Accessory Type	Screwlock	
For Use With	D Connector	
Gender	Female	
Finish	Zinc	
Thread Size	4-40 UNC	
Application	Preventing mechanical stress, provide EMI/RFI shielding and protection from the elements, Industrial, commercial and domestic applications and environments	

#### **Mechanical Specifications**

Screw Length	13mm
--------------	------

## **Approvals**

Compliance/Certifications ANSI/ESD S20.20:2014 and BS EN 61	1340-5-1:2007
---	---------------



