EAO – Your Expert Partner for **Human Machine Interfaces**

82-5551.1123 - Illuminated pushbutton 19 mm Aluminium, momentary

82-5551.1123 - Illuminated pushbutton 19 mm Aluminium, momentary



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

 $\begin{array}{ll} \mbox{Mounting cut-out} & \mbox{\varnothing 19 mm} \\ \mbox{Design} & \mbox{flush} \end{array}$

Front

Front dimension Ø 22 mm
Front shape round
Front ring shape flush
Front bezel material Aluminium

Other Attributes

Operating voltage 12 V AC/DC Weight 0,018 kg Operation current 7 mA

Operating-/Indication part

Lens optics opaque
Lens material Aluminium
Lens profile flat
Lens illumination illuminative
Lens colour natural anodized

IP-Rating

Front protection IP65, IP67

Connection Method

Terminal Solder 2.8 x 0.5 mm

Actuator

Switching action Momentary

Switching element

Switching current 3 A
Contact material Silver
Contacts 1 C

Switching system Snap-action switching element

Switching voltage 240 V AC/DC

Illumination

Illumination Ring with blue LED

Function


Illuminated pushbutton

e a o


EAO – Your Expert Partner for **Human Machine Interfaces**

82-5551.1123 - Illuminated pushbutton 19 mm Aluminium, momentary


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Legend

Switching action: B = Momentary Contacts: C = Changeover