EAO – Your Expert Partner for **Human Machine Interfaces**

82-6561.1000 - Pushbutton 22 mm Aluminium

82-6561.1000 - Pushbutton 22 mm Aluminium



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Design flush
Mounting cut-out Ø 22,3 mm

Front

Front shape round
Front ring shape flush
Front dimension Ø 25 mm
Front bezel material Aluminium

Other Attributes

Weight 0,020 kg

Operating-/Indication part

Lens optics opaque
Lens material Aluminium
Lens colour natural anodized

Lens profile flat

Lens illumination non-illuminative

IP-Rating

Front protection IP65, IP67

Connection Method

Terminal Solder 2.8 x 0.5 mm

Actuator

Switching action Momentary

Switching element

Switching current 3 A
Contact material Silver
Contacts 1 C

Switching system Snap-action switching element

Switching voltage 240 V AC/DC

Function


Pushbutton

e a o


EAO – Your Expert Partner for **Human Machine Interfaces**

82-6561.1000 - Pushbutton 22 mm Aluminium


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Legend

Switching action: B = Momentary Contacts: C = Changeover