

FEATURES

- Lids with black neoprene gasket and 4 x M6 captive hexagon headed screws
- Operating temperature -20°C to +110°C
- Multiple DIN rail fixing points, M5
- External M6 earthing stud
- Manufactured from stainless steel offering excellent durability and corrosion resistance
- IP66 rating offering excellent weatherproof protection
- Suitable for a wide range of applications indoors and outdoors

RS PRO Junction Boxes

RS Stock No.: 8428330



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS PRO Stainless Steel Terminal Box, IP66, Unpainted

Introducing stainless steel terminal boxes from RS PRO, a range of high quality and durable terminal box enclosures for housing DIN rail terminals and accessories in a range of electrical applications. With multiple DIN rail fixing points included, these junction boxes are perfect for installing and protecting electrical wires, connectors and cables, as well as providing a protective case for switches and more.

These junction boxes are manufactured from stainless steel, offering a highly durable and sturdy enclosure that can be installed in a wide range of environments. The terminal boxes also feature a black neoprene gasket with an IP66 rating, offering excellent weatherproof protection making them ideal for use both indoors and outdoors. These RS PRO stainless steel terminal boxes also feature a wide operating temperature of -20 to +110°C making them highly versatile, allowing them to be used in environments with varied temperatures.

General Specifications

Body Material	1.2mm AISI 304 finish stainless steel				
Base Material	1.2mm AISI 304 finish stainless steel				
Gasket Material	A black neoprene				
Application	Power Management				
Colour	Unpainted				
Lid Colour	Unpainted				
Temperature Range	-20°C to +110°C				
Shape	Rectangular				
Surface Finishing	Untreated				
Size	Small				
Cover Locking	Screw				

Mechanical Specifications

External Length	150 mm	
External Width	150 mm	
External Height	80 mm	
Internal Dimensions	150 x 150 x 80mm	

Protection Category

IP Rating	IP66



Approvals

Declarations	RoHS Certificate of Compliance
Dooral attorio	Notice Commission of Compilation

Similar Products

Stock No.	Brand	Product Name	Material	Dimensions
1444457	RS PRO	Junction Box	Glass Reinforced Polystyrene	220mm x 120mm x 90mm
749-1857	RS PRO	Junction Box	Stainless Steel	150mm x 80mm x 150mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

I



