

FEATURES

- AISI 304 Stainless Steel
- IP66 rating
- Fully wall mountable
- Lockable

RS PRO Wall Boxes- 304 Stainless Steel Wall Box

RS Stock No.: 842-8346



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS Pro IP66 Sheet Steel Wall Boxes

From RS Pro, a range of incredibly useful steel wall mounted enclosures. Enclosures are present in almost every industry and can store all manor of items, such as medical equipment or electronics. These boxes are rated at IP66 and provide an excellent degree of protection, whether it's used within an indoor or outdoor environment. With various sizes available, they are suitable for a wide selection of applications. All models are highly reliable and excellent quality.

General Specifications

Body Material	Steel
Number Of Doors	1
Colour	Unpainted
Gland Plate	No
Door Lock Type	Single Lock System
Chassis Plate	Zinc-coated steel
Transparent Door	No
Fixing Kit	Yes
Application	Electrical
External Mounting Type	Bracket
Internal Mounting Type	Panel
Special Features	IK10 Against Mechanical Impacts
For Protection Of	Sensitive Electrical Equipment
Sealing Gasket	No

Mechanical Specifications

External Height	600 mm
External Depth	200 mm
External Width	400 mm
Dimensions	H 600 mm x D 200 mm x W 400 mm
Thickness	Enclosure & door 1.2mm or 1.5mm sheet steel

Protection Category

IP Rating	IP66
------------------	-------------

Approvals

Declarations	RoHS Certificate of Compliance
---------------------	---------------------------------------

Similar Products

Stock No.	Brand	Product Name	Colour	Body Material	Dimensions
775-5300	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 250 mm x 150 mm
775-5788	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 200 mm x 150 mm

Additional Information / Installation Diagrams / Illustrations / Accessories

