

FEATURES

- AISI 304 Stainless Steel
- IP66 rating
- Fully wall mountable
- Lockable

RS PRO Wall Boxes-304 Stainless Steel Wall Box

RS Stock No.: 842-8403



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS Pro IP66 Stainless Steel Wall Box

Brought to you by RS Pro, A range of stainless steel wall mounted enclosures. Enclosures are present in almost every industry and can store all manor of items, such as medical equipment or electronics. These boxes are rated at IP66 and provide an excellent degree of protection, whether it's used within an indoor or outdoor environment. With various sizes available, they are suitable for a wide selection of applications. All models are highly reliable and excellent quality.

General Specifications

Body Material	304 Stainless Steel		
Number Of Doors	1		
Colour	Unpainted		
Gland Plate	No		
Sealing Gasket	No		
Door Lock Type	Single Lock System		
Chassis Plate	Zinc-coated steel		
Transparent Door	No		
Fixing Kit	Yes		
Application	Electrical		
External Mounting Type	Bracket		
Internal Mounting Type	Panel		
Special Features	IK10 Against Mechanical Impacts		
For Protection Of	Sensitive Electrical Equipment		

Mechanical Specifications

External Height	500 mm
External Width	250 mm
External Depth	400mm
Dimensions	500 x 250 x400 mm
Thickness	1.2 mm for enclosure & door

Protection Category

IP Rating	IP66
-----------	------



Approvals

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

Similar Products

Stock No.	Brand	Product Name	Colour	Body Material	Dimensions
775-5300	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 250 mm x 150 mm
775-5788	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 200 mm x 150 mm

Additional Information / Installation Diagrams / Illustrations / Accessories

