

# Timer switches

## Mechanical timer switches

- 24h, 16A/230V~/3680W
- Plastic version with shutter
- Easy to use

#	
---	---

### Timer switch

852.101	White   121 x 74 x 76 mm (LxWxH)   Smallest possible switching interval: 15 minutes   96 switch-on and switch-off times possible per day (24 h)
---------	---

### IP44 timer switch

852.107	Splash-proof   129x59x86 mm (LxWxH)   With transparent hinged lid   Suitable for use in damp environments   Operating temperature range: -25 °C to +55 °C   Smallest possible switching interval: 30 minutes   48 switch-on and switch-off times possible per day (24 h)
---------	--

### Mini timer switch

852.104	White   103x54x70 mm (LxWxH)   Smallest possible switching interval: 30 minutes   48 switch-on and switch-off times possible per day (24 h)   Switch to override timer function
---------	---

## Digital timer switch

- 24h, 16A/230V~/3680W
- Plastic version with LCD display, with shutter
- Easy to use
- Integrated, rechargeable battery

#	
---	---

852.103	White   120x64x76 mm (LxWxH)   Smallest possible switching interval: 1 minute   Programmable by the day or by the week   Built-in random generator   Countdown function   Resettable
---------	--



852.101



852.107



852.104



852.103