



MASTER LEDbulb

MAS LEDbulb DT 8.5-60W E27 A60 CL

The MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. They are particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimizes maintenance cost without any compromise on light quality. They can be used together with most leading-edge dimmers, enabling further efficiencies while helping to create the desired atmosphere.

Product data

General Information	
Cap-Base	E27 [E27]
Reddot Design Award Winner mark	Reddot Design Award Winner 2016
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	8.5-60W
Light Technical	
Color Code	822-827 [tunable warm white]
Luminous Flux (Nom)	806 lm
Luminous Flux (Rated) (Nom)	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2200-2700 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %	
Operating and Electrical		
Input Frequency	50 to 60 Hz	
Power (Rated) (Nom)	8.5 W	-
Lamp Current (Nom)	45 mA	
Wattage Equivalent	60 W	
Starting Time (Nom)	0.5 s	
Warm Up Time To 60% Light (Nom)	0.5 s	
Power Factor (Nom)	0.7	
Voltage (Nom)	220-240 V	
Temperature		
T-Case Maximum (Nom)	110 °C	

Datasheet, 2017, January 31 data subject to change

MASTER LEDbulb


Controls and Dimming		
Dimmable	Yes	
Mechanical and Housing		
Bulb Finish	Clear	
Approval and Application		
Energy Saving Product	Yes	
Suitable For Accent Lighting	No	
Energy Efficiency Label (EEL)	A+	
Energy Consumption kWh/1000 h	9 kWh	

Product Data		
Full product code	871869648132500	
Order product name	MAS LEDbulb DT 8.5-60W E27 A60 CL	
EAN/UPC - Product	8718696481325	
Order code	929001150932	
Numerator - Quantity Per Pack	1	
Numerator - Packs per outer box	10	
Material Nr. (12NC)	929001150932	
Net Weight (Piece)	0.076 kg	

Warnings and Safety


- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Dimensional drawing



Product	D	С
MAS LEDbulb DT 8.5-60W E27 A60 CL	60 mm	110 mm

Photometric data



MASTER LEDbulb

