

FEATURES

- High impact textured low profile aluminium alloy cover
- Warp proof self-extinguishing UL approved PVC base
- Maximum service temperature of 85°C
- Self-adhesive tape applied to the PVC base for quick easy installation

RS PRO Grey Floor Trunking, W70 mm x D16mm, L1m, Aluminium Alloy (Lid), PVC (Base)

RS Stock No.: 880-6869



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro, a range of aluminium floor cable trunking designed for mounting on floors for routing low voltage and signal wires in high traffic areas. This trunking consists of a warp proof self-extinguishing PVC inner rail and a low profile high impact decorative convex extruded aluminium top cover. The PVC base is self-adhesive and the aluminium cover is securely dovetails over the top. All models are highly reliable and excellent quality.

General Specifications

Trunking/Chain Type	Floor Trunking
Material	Aluminium Alloy (Lid), PVC (Base)
Colour	Grey
Fire Behaviour	Self-extinguishing
Type of Fastening	Self-adhesive
Applications	Hospital, Football grounds , Factories, Conference Centres, Schools, Colleges and Universities

Mechanical Specifications

Length	1m
Width	70mm
Depth	16mm

Operation Environment Specifications

Maximum Service Temperature	85°C
------------------------------------	------

Approvals

Standards Met

UL 94 V-0, RoHS Compliant

