



Well-proven classic – now even better.  
Alligator® with 30 % more gripping capacity.

Alligator®



- ▶ optimised adjusting mechanism now with 9 adjustment positions
- ▶ improved access to the workpiece due to very slim head shape
- ▶ capacity now:  
up to 46 mm width across flats,  
pipes up to 2" diameter

**NEW**

**KNIPEX** Quality – Made in Germany

# Alligator® with triple optimisation.



88 01 250

## Proven tool – now even better!

KNIPEX has increased the gripping capacity of the Alligator® by 30% and it now has 9 adjusting positions instead of the previous 7. The water pump pliers now fit even more comfortably into the hand and its slimmer head shape allows even better access to workpieces in confined areas.



The Alligator® grips hexagon nuts and bolt heads with widths of up to 46 mm A/F. Expanded gripping capacity up to 2" pipes. Great achievements for a tool of 250 mm in length!



## Time-tested reliable Alligator® with new advantages:

- slimmer head shape for improved access to the workpiece
- ergonomically optimised handles for a more comfortable grip
- box joint with double guide for high stability
- self-locking on pipes and nuts to prevent slipping on the workpiece, low handforce required
- guard prevents operators' fingers being pinched
- favourable lever action with optimum transmission of force
- gripping surfaces with special hardened teeth (approx. 61 HRC)
- continuous reliable gripping thanks to high wear-resistance
- chrome vanadium electric steel, forged, oil-hardened



Article-No.	EAN 4003773-	Finish	⊘	⊞ mm	Adjustment positions	↔ mm	⚖ g	
88 01 250	022992	head polished, handles with non-slip plastic	2"	46	9	250	320	
88 02 250	019282	head polished, with two-colour dual component handles	2"	46	9	250	355	
88 03 250	005742	head chrome plated, handles with non-slip plastic coating	2"	46	9	250	315	
88 05 250	035497	head chrome plated, with two-colour dual component handles	2"	46	9	250	355	
88 06 250	039303	head chrome plated, insulated with two-colour dual component handles, VDE-tested	2"	46	9	250	375	 ⚡ 1000V
88 07 250	019343	head chrome plated, handles plastic dipped insulated, VDE-tested	2"	46	9	250	420	 ⚡ 1000V

Your distributor



## KNIPEX-Werk C. Gustav Putsch KG

Oberkamper Strasse 13  
42349 Wuppertal (Germany)

Tel.: +49 (0) 202 – 47 94-0

Fax: +49 (0) 202 – 47 74 94

info@knipex.de

www.knipex.de