

FEATURES

- Surface mounting
- Wire termination
- Includes overload protection
- Clockwise knob rotation
- Single phase
- Single output
- Primary voltage rating of 240 V
- Secondary voltage rating of 0 - 240 V, 0 - 270 V
- Power rating of 2.4 KVA
- Primary current rating of 10 A
- Operating frequency range of 50 - 60 Hz
- Weight of 9.4 kg
- Measures 175 mm x 175 mm x 170 mm

RS PRO 1 Phase 2.4KVA Variac, 1 Output, 240V, 10A

RS Stock No.: 890-2819



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO variac transformer is made for surface, floor or wall mounting. It features an enclosed construction, has a long life span and needs little maintenance, so will save you time. Its silver-plated commutator means the transformer offers smooth linear output, with no waveform distortion and integrated overload protection. This transformer regulates well as a result of its continuously variable AC output voltage and an overvoltage tap. It has a low operating torque and a low magnetising current making it very efficient. With its screw terminals, it's also easy to mount.

General Specifications

Number of Outputs	1
Knob Rotation	Clockwise
Construction	Enclosed
Protection Features	Overload protection
Applications	Industrial and domestic

Electrical Specifications

Number of Phases	1
Power Rating	2.4kVA
Primary Voltage Rating	240V
Secondary Voltage Rating	0V to 240V, 0V to 270V
Primary Current Rating	10A
Maximum Operating Frequency	50Hz
Minimum Operating Frequency	60Hz
Termination Type	Wire Termination

Mechanical Specifications

Mounting Type	Surface Mount
Dimensions	175mm x 175mm x 170mm
Depth	170mm
Length	175mm
Width	175mm
Weight	9.4kg

Approvals

Compliance/Certifications	EN61340
Standards Met	RoHS

