




Datasheet

High Dome

RS Stock 896-2094



Dimensions: (mm)



Specifications

Connection Type: 2Pole + Earth Voltage: 250V AC

VAC / 250 VAC

Approvals: NA
Standard: NA
Mounting: Screw Type

Type: HD-Socket (HI-DOME) – Illuminated

Socket Type:

Mounting:

Material For Rubber Gasket:

Material Body:

Type A

M3 Screw

Nitril / Silicon

Nylon-6 GF

Gland Size:

Body Colours:

Contact Resistance:

Current Caring Parts:

Ryion-b GF
PG-9

Black, Grey
20m Ohms max
Copper alloy / Tin plated

Rating: 10A 110VAC, 230VAC Terminals: Screw-type

H.V Breakdown Test: 2 KV AC For 1 Minute Insulation Resistance: 100 M Ohms min.